



WR-22 Waveguide Short Plate, UG-Cover Round Flange, 4mm Copper

Waveguide Accessories Technical Data Sheet

PEW22SP4

Features

- WR-22 Waveguide Short Plate
- Round UG-Cover Flange Configuration
- Frequency Range: 33 GHz to 50 GHz
- Min VSWR: 60:1
- 4 mm Thick Copper Construction

Description

PEW22SP4 is a fixed WR-22 waveguide short (shorting plate) with operating frequency range from 33 GHz to 50 GHz. This waveguide short is fabricated with 4 mm thick copper by high precision manufacturing process. PEW22SP4 has a Round UG-Cover configuration and provides high reflection short circuit for WR-22 waveguide components. Along with Pasternack's waveguide shim products, the waveguide short is ideal for TRL (Thru, Reflect, Line) calibration for RF test instruments. Pasternack offers a wide selection of waveguide components with high performance available in stock and same-day shipping to customers worldwide.

Mechanical Specifications

Body Material	Copper
Body Finish	Gold Plating
Length	0.158 in [4.01 mm]
Width	1.126 in [28.6 mm]
Height	1.126 in [28.6 mm]
Weight	0.022 lbs [9.98 g]

Compliance Certifications (see [product page](#) for current document)

WR-22 Waveguide Short Plate, UG-Cover Round Flange, 4mm Copper from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [WR-22 Waveguide Short Plate, UG-Cover Round Flange, 4mm Copper PEW22SP4](#)


URL: <https://www.pasternack.com/pew22sp4-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.


PEW22SP4 CAD Drawing

WR-22 Waveguide Short Plate, UG-Cover Round Flange, 4mm Copper

REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	1/28/2020	S-PONG



WR-22 WAVEGUIDE
UG-383/U ROUND COVER FLANGE



UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
 .X = ±.2 [5.08] FRACTIONS ± 1/32
 .XX = ±.02 [.51] ANGLES ± 1°
 .XXX = ±.005 [.13]

CABLE LENGTH (L) TOLERANCES:
 L ≤ 12 [305] = +1 [25] / -0
 12 [305] < L ≤ 60 [1524] = +2 [51] / -0
 60 [1524] < L ≤ 120 [3048] = +4 [102] / -0
 120 [3048] < L ≤ 300 [7620] = +6 [152] / -0
 300 [7620] < L = +5% L / -0

ALL DIMENSIONS SHOWN
ARE FOR REFERENCE ONLY.

PE PASTERNAK
an INFINIT® brand

Pasternack Enterprises, Inc.
P. O. Box 16759, Irvine, CA 92623.
Phone: 1.949.261.1920 | 1.866.727.8376
Fax: 1.949.261.7451
Website: www.pasternack.com
E-mail: sales@pasternack.com

THIRD-ANGLE PROJECTION

THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNAK CORPORATION. ALL RIGHTS RESERVED.

SHEET 1 OF 1
SCALE N/A

REV A
ITEM NO. PEW22SP4
DRAWN BY K.DANG