
NOTICE OF PROPRIETARY RIGHTS
THIS DOCUMENT CONTAINS CONFIDENTIAL TECHNICAL DATA, INCLUDING TRADE SECRETS, PROPRIETARY TO
TIMES MICROWAVE SYSTEMS. DISCLOSURE OF THIS DATA IS EXPRESSLY CONDITIONED UPON YOUR ASSENT THAT ITS USE IS LIMITED TO USE WITHIN
YOUR COMPANY ONLY. ANY OTHER USE IS STRICTLY PROHIBITED WITHOUT THE PRIOR WRITTEN CONSENT OF TIMES MICROWAVE SYSTEMS.

MYS	REVISION DESCRIPTION		DFTM	DATE	APPD	DATE
Α	RELEASED FOR	PRODUCTION	n.n.n	11/7/13	J.D.B.	11/7/13



	BODY	CONTACT
Α	LBALOY	GOLD/NI

1.0 PERFORMANCE

1.1 FREQUENCY RANGE: DC-4 GHz

1.2 NOMINAL IMPEDANCE: 50 OHMS

1.3 DWV: 500 VRMS @ 60 Hz (SEA LEVEL)

1.4 TEMPERATURE RANGE: -65°C TO +165°C 2.4 CRIMP FERRULE: SOFT COPPER

2.0 MATERIALS

2.1 DIELECTRIC: PTFE

2.2 CONTACT: BRASS

2.5 OTHER METAL PARTS: BRASS

2.6 GASKET: SILICONE RUBBER

2.7 HEAT SHRINK: POLYOLEFIN THICK WALL

3.0 FINISHES: SEE TABLE

4.0 MECHANICAL

2.3 SPRING WASHER: BERYLLIUM COPPER 4.1 INTERFACE PER MIL-STD-348

MATL:	UNLESS OTHERWISE SPECIFIED	DFTM.N.N.N	TIMES MICDOVAVE SYSTEMS
	ALL DIMENSIONS ARE IN INCHES MACHINED SURFACES FINISH N/A RMS MAX.	DATE 11/7/13	TIMES MICROWAVE SYSTEMS
	REMOVE ALL BURRS .005 MAX. BREAK MACHINE CORNERS .005 MAX. FILLET R.	CHKD. J. D. B.	TC-200-BM-X
USED DN: A	TOLERANCES ON DECIMALS	DATE 11/7/13	BNCM
	.XX ±.03 .XXX ±.005 ANGLES ±1° FRACTIONS ± 1/32	APPD. J. D. B.	FOR LMR-200 CABLE
SCALE: N/A DWG. A	DO NOT SCALE DRAWING CODE 68999	DATE 11/7/13	🖁 1 of 1 SD3190-2883 🖁 A